

OP 692-6

UV Resistant Optoelectronic Epoxy

Description

OP 692-6 is a clear, water-white UV resistant epoxy system suitable for encapsulation of high performance optoelectronic devices like indicator lamps. This system is cured with anhydride hardeners. It is recommended for encapsulation of LED chips and components, bonding of electronic parts, most plastics, ceramics and metals. This epoxy system contains multifunctional resins which give excellent performances in temperature cycling, high temperature storage, high humidity storage, minimal light output degradation, and outdoor weathering. It is enhanced for maximum resistance to moisture absorption, crack resistance from thermo-mechanical stresses, high temperature degradation and increased adhesion to most substrates. It is specially improved to provide excellent resistance to UV and thermal yellowing.

Applications

1. Encapsulation of high performance LED lamps devices

Properties

Property	Unit	Typical Value		
		Part A Resin	Part B Hardener	Mixed
Chemical type		Epoxy	Anhydride	
Appearance		Blue liquid	Yellow Liquid	
Mix ratio, by weight		1.0 ± 0.02	1.0 ± 0.02	
Shelf life, 25°C	Month	12	12	
Pot life, 25°C	Hour			3
Viscosity, CAP 1 / rpm 30, 25°C	cP	950	250	550
Refractive index, 25°C		1.49	1.48	1.49
Hardness	Shore D			85
Tg, DSC	°C			135

Recommended Cure

Schedule	Temp.	Cure Time
Pre cure	120°C	2 hr
Post cure	150°C	2 hr

Guidelines for Use

1. Agitate the Part A resin and Part B hardener in their original bottles before use. Either of these parts may crystallize on storage at low temperatures. However, warming and stirring of these individual parts at 70°C will ensure homogeneity.
2. Mix Part A resin and Part B hardener in the ratio of 1.0 : 1.0 by weight.
3. Remove the air bubbles in the epoxy mix by vacuum degas at 0.001 mbar (0.1 Pa) for 20 minutes.
4. The epoxy mix can be dispensed with a syringe into mold cups.

5. Cure the epoxy at 120°C for 2 hours. Remove the hardened epoxy from the mold cups. Further cure the epoxy at 150°C for 2 hours.
6. Wear rubber gloves when handling epoxy resins and epoxy hardeners.
7. Wipe off any uncured epoxy spillage with tissue or dry cloth. Further cleaning may be achieved with tissue wetted with iso-propanol.

Storage

Store both Part A resin and Part B hardener in a cool, dark place to prolong shelf life. They must be kept away from sunlight and bright room lights.

Part B is moisture sensitive. Close the seal and cap of the bottle tightly immediately after use.

Packaging

- 1 kg plastic bottle
- 5 kg plastic bottle

Environment, Health & Safety

This product is RoHS compliant.
It does not contain any known
carcinogenic, mutagenic or
teratogenic component.

Contact Information

Penchem TechnologiesSdn Bhd
(767120-A), 1015, Jalan
Perindustrian Bukit Minyak
7,14100 Penang, Malaysia
T: +604-5015976, 77,78
F: +604-5015979
E: enquiry@penchem.com
W: www.penchem.com

Revision 1: 25-Sep-15.KF