

UV 566-20

Structural UV Epoxy

Description

UV 566-20 is a fast cure, medium viscosity UV-curable epoxy system. The cured material has excellent flexibility, good toughness and good adhesion to a variety of substrates including metals and plastics. It has low odor, and low skin and eye irritation potential. It does not contain volatiles and is very suitable for electronic applications. It is not inhibited by oxygen during UV cure, has low shrinkage, high gloss and good resistance to yellowing. The thixotropy has been adjusted to control excessive overflow.

Applications

1. UV curable adhesive for plastics and metals.

Guidelines for Use

1. Thaw the epoxy to room temperature (25°C) before use.
2. Dispense the epoxy by using a syringe.
3. Wipe off any excess uncured adhesive with a piece of dry cloth or tissue. Further cleaning may be achieved with tissue dabbed with isopropanol alcohol (IPA).
4. Expose the epoxy to long UV wavelength light in the 320-380 nm range at 1000 mW/cm² for 3 seconds.
5. If necessary, ultimate properties may be obtained faster by additional curing of the epoxy in a convection oven at 120°C or higher for 30 minutes or longer time.

Properties

Property	Test Method	Unit	Typical Value
Chemical type	-	-	Epoxy
Appearance	Pen 10	-	Translucent liquid
Mix ratio, by weight	-	-	One component
Shelf life, -20°C	Pen 26	Month	6
Pot life, 25°C	Pen 57	Day	7
Viscosity, 25°C, 5rpm	Pen 44	cP	6500
Thixotropic Index	Pen 37	-	3.5
Flow Test 45 degree, 25°C, 30min	Pen 15	mm	0
Refractive index, 25°C, 589nm	Pen 28	-	1.484
Density	Pen 61	g/cm ³	1.269
Hardness	Pen 29	Shore D	75
Die Shear Strength_ UV _ metal chip to glass	Pen 36	kgf	7
Die Shear Strength_ UV+Heat _ metal chip to glass	Pen 36	kgf	9
Tg	Pen 64	°C	86
CTE, alpha-1	Pen 64	ppm/K	51
CTE, alpha-2	Pen 64	ppm/K	143
Water boil, wt gain, 100°C/1hr	Pen 21	%	1.4

Recommended Cure

Pre-Cure

UV (mW/cm ²)	Cure time
1000	3 sec
500	6 sec
200	15 sec

Post Cure

Temp.	Cure Time
120 °C	30 min

Storage

Tightly close original container of unused product. Store below -20°C. Storing at lower temperatures down to -40°C may prolong shelf life beyond 6 months. However it may take longer time to thaw the product.

Packaging

- 5ml Black EFD Syringe
- 10ml Black EFD Syringe
- 30ml Black EFD Syringe

Environment, Health & Safety

This product is RoHS compliant. It does not contain any known carcinogenic, mutagenic or teratogenic components.

Contact Information

Penchem Technologies Sdn Bhd
(767120-A), 1015, Jalan Perindustrian Bukit Minyak 7, 14100 Penang, Malaysia
T: +604-501 5976, 77, 78, 79
E: enquiry@penchem.com
W: www.penchem.com

Revision 5.3-Jul-18.LT